



# BLOCKING FOR FREEDOM CLIMBER

For walls being prepared to support the Freedom Climber, the drawing below gives the location where 2 x 6 blocking can be located to both stiffen the wall and provide extra material to affix the Freedom Climber frame. The first band of blocking is 3' 8.25" from the floor to the bottom edge of the blocking; and the second band of blocking is 7' 3.5" from the floor to the bottom edge of that blocking. The blocking can be used for both wood and metal studs.



# RECEPTACLE LOCATION FOR THE DIGITAL DISPLAY

The Freedom Climber is 110' wide. Find the center where the Freedom Climber is to be located and measure to the right 4'-2" and measure up 16". The location is shown below as the green square. This put the receptacle out of view but easily accessible if need be.

